

# FLEXINOX Apron (PPE - category III)



#### FIELD OF APPLICATION

The FLEXINOX apron is made with 100% food contact approved stainless steel. It is used by butchers in meat industries, Horeca, supermarkets and many other fields such as textile industry... It ensures cut-protection against any risks with hand knives, hand cutting tools or stabbing.

MATERIAL: 100% stainless steel detectable plates

#### **FEATURES**

The upper part of the apron is equipped with four fixing points (double fixing plate).

Thanks to its exclusive and patented assembly system, the FLEXINOX apron is reversible.

Possibility to add a press-studs apron or a cover for maximum hygiene and ease of cleaning.









#### **NORMS & REGULATIONS**

The FLEXINOX apron complies with the regulation (UE) PPE 2016/425.

EN ISO13998 (2003) performance level 2: suitable for boning operations.

Notified body in charge of the certification:

N° 2777 SATRA Technology Europe Ltd, Bracetown Business Park, Clonee, Co. Meath - D15 YN2P – Ireland **Notified body involved in manufacturing control**: N° 0333 AFNOR certification

11 rue Francis De Pressensé - 93571 - La Plaine Saint-Denis



## CLEANING CONDITIONS

**Cleaning / Disinfection:** PPE can be cleaned using a suitable washing gun, by soaking, by vigorous brushing or in a washing machine. In all cases, the water with added product must be at a maximum temperature of 63 ° C.

Warning: the technical sheet of the product used refers to a maximum water temperature, which may be lower.

Particular attention to dosage and temperature must be observed in the case of using alkaline chlorinated or acidic products. Use only products authorized by the veterinary services. The use of chlorine in large doses and at high temperature is not recommended.

**Disinfection:** High temperature disinfection can be done with clean water of a minimum of 82 ° C up to a maximum temperature of 90 ° C, in a machine, by soaking or sprinkling.

Drying and Storage: Forced drying by hot or natural air ventilation but in a dry and ventilated place. Store in a cool, dry place

### **SIZE AND REFERENCES:**

Width x height (cm)	Reference	Weight (grams)	Operator's size	Waist / chest measurement
40 x 67	0XFL170.11.040X067	1250 g	< 158	< 88
45 x 72	0XFL170.11.045X072	1470 g	< 170	< 100
55 x 70	0XFL170.12.055X070	1670 g	< 166	< 120
55 x 80	0XFL170.12.055X080	1860 g	< 188	< 120

N° intrastat : 73239390



